

FEATURES

- IP44 ingress protection
- Made from a toughened engineering plastic
- High thermal stability
- High mechanical strength
- Halogen free
- Self-extinguishing
- Ribbed finger tab on lid for one handed opening
- Excellent corrosion and abrasion resistance

RS PRO IP44 Blue Cable Mount 2P+E Industrial Power Socket, Rated At 16.0A, 230.0V

RS Stock No.: 724-9108



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS Pro, a range of IP44 splash proof industrial cable mount plugs that are reliable and simple to assemble. The outer casing and inner contact carrier are constructed from a toughened engineering material designed to provide high thermal stability and mechanical strength. Nickel plated brass contact pins ensure excellent corrosion and abrasion resistance. A domed cable gland at the rear of the splash proof connector provide external cable clamping and additional support. Stylishly designed, the RS Pro range of industrial BS4343 plugs perform extremely well in the most challenging environments. All models are highly reliable and excellent quality.

Power plug [724-9088](#) mates with Connector (socket) [724-9108](#)

Power plug [724-9079](#) mates with Connector (socket) [724-9104](#)

Power plug [724-9081](#) mates with Connector (socket) [724-9117](#)

Power plug [724-9085](#) mates with Connector (socket) [724-9110](#)

Power plug [724-9091](#) mates with Connector (socket) [724-9126](#)

Power plug [724-9097](#) mates with Connector (socket) [724-9123](#)

General Specifications

Pole Format	2P+E
Gender	Female
Body Orientation	Straight
Material	Engineering Plastic
Colour	Blue
Applications	Providing power for machinery on construction sites, Woodworking machines, Maintenance workshops in the light industry

Electrical Specifications

Current Rating	16A
Voltage Rating	230V
Plug/Socket	Socket
Termination Method	Screw
Cable CSA	2.5mm ²
Contact Material	Nickel plating Brass

Mechanical Specifications

Mounting Type

Cable Mount

Protection Category

IP Rating

IP44

Approvals

Compliance/Certifications

EN 60309-1, EN 60309-2

