



PRODUCT BRIEF

RS 471-6866

PRODUCT:

HL19

APN: 9311644011033

TUN: 19311644011030

PRODUCT DESCRIPTION

Twin 500W Halogen Floodlights on Tripod

FEATURES

- Diecast Aluminium/Zinc Alloy Lanterns
- Supplied with 500 watt halogen linear tungsten tube 118mm (replace with Arlec HT500). Brightness approx 10000 lumen, colour temperature 3000K, average life 3000 hours.
- Weatherproof rating IP44
- Adjustable tubular metal tripod stand - Max height 1.8 metres, packs down to 0.7 metre long
- Safety grille on face of lanterns
- High temperature tempered glass faces
- 1.8 metre mains cord on each lantern
- Packaged in colour printed carton (Size 695 x 160 x 265 mm)
- Country of origin: China

