


## UNIVERSAL CALIPER - 150MM - 1/20TH | 816




### Norm :

**NF EN ISO 13385-1, ISO 13385-1, DIN 862**

### Description

- Accuracy: 1/20th - 0.05 mm.
- Interior, exterior, depth measurement.
- Stainless steel rule - mat finish.
- Rule hardness: 40 HRc minimum.
- Flat depth gauge.
- Vernier with guide for better thumb position.
- Vernier endurance: 20 000 cycles minimum.
- Vernier screw locking.
- Supplied in case with compliance certificate.

### Information



A [mm]	150
--------	-----

C [mm]	40
--------	----

E [mm]	16
--------	----

L [mm]	228
--------	-----

[g]	288
-----	-----