MODULAR RELEASABLE POKE-IN CONNECTOR

TE Connectivity (TE) introduces the Modular Releasable Poke-in Connector, a 4.0mm pitch modular connector for wire to board connectivity. The Poke-in feature allows for easy and fast installation and its modular design enables a flexible solution. The low profile, high density and compact design enables broad usage in, for instance, telecommunication systems, lighting systems, security and wire arrangement of architectures.



Applications

- LED Lighting
- Telecommunication
- Security
- Other wire-to-board applications

Electrical

• Current rating: 6A with 18 AWG / 5A with

20 AWG & 22 AWG

Voltage rating: 400 VAC MaxDielectric strength: 1800 VAC

Mechanical

• Operating Temperature: -40°C- + 105°

Product Specifications

Application Specification: 114-137055
 Product Specification: 108-137055
 UL Approval: UL1977

• IEC60838 comply with clause 15 of IEC 60598-1

Materials


• Contact: Copper Alloy with Tin plating


Key Benefits


- Modular Technology enables flexibility in design
- Easy and fast installation with Poke-in feature
- · 4.0mm pitch, modular position type.
- Compact size design for space saving
- Compliance with UL1977 / File: E28476
- Compliance with IEC 60598-1:2014
 & IEC 60998-1:2002




Dimensions











Product Selection Information

Part Number	Description
2834006-1	Terminal Blocks / Poke-In Connectors
2834006-2	Terminal Blocks / Poke-In Connectors
2834006-3	Terminal Blocks / Poke-In Connectors
1-2834006-2	Terminal Blocks / Poke-In Connectors

te.com

© 2016 TE Connectivity Ltd. Family of Companies. All Rights Reserved. TE, TE Connectivity, and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and company names mentioned herein may be trademarks of their respective owners.

1-1773872-8 JN 1/16

USA: +1 (800) 522-6752 Canada: +1 (905) 475-6222 Mexico: +52 (0) 55-1106-0800 Latin/5. America: +54 (0) 11-4733-2200 Germany: +49 (0) 6251-133-1999 UK: +44 (0) 800-267666 France: +33 (0) 1-3420-8686 The Netherlands: +31 (0) 73-6246-999 China: +86 (0) 400-820-6015

