

MARQUARDT



SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

single-pole		Changeover switch with OFF position in the center (SPDT - Center OFF)								Changeover switch (SPDT momentary)				
		18.08.1 302	18.08.2 102	18.08.2 302	18.08.2 704	18.08.6 102	18.08.6 103	18.08.6 202	18.08.6 302	18.08.1 152	18.08.1 353	18.03.6 222	18.03.1 202	18.03.1 252
Lighting voltage (V)														
Actuator color / printing		■	■	■	■	■	■	■	■	■	■	■	■	■
Housing color		■	■	■	■	■	■	■	■	■	■	■	■	■
12 (4) A 250 V AC 1E4														
10 (4) A 250 V AC 1E4												○		
8 (8) A 250 V AC 5E4												○		
6 (4) A 250 V AC 5E4														
6 (2) A 250 V AC 1E4		○	○	○	○	○	○	○	○					
4 (3) A 250 V AC 6E3														
4 (2) A 250 V AC 1E4													○	
30 mA 12 V DC 5E4										○	○			○
15 A 250 V AC 1 1/2 HP														
15 A 125 V AC 3/4 HP														
10 A 250 V AC 1/2 HP												○		
10 A 125 V AC 1/3 HP												○		
6 A 250 V AC 1/2 HP														
6 A 125 V AC 1/4 HP														
6 A 125 - 250 V AC 1/8 HP		○	○	○	○	○	○	○	○					
6 A 125 V AC 1/10 HP													○	
4 A 250 V AC 1/10 HP													○	
Terminal type		U	U	U	U	U	U	U	U	U	U	U	U	U
Terminal description		4.8								4.8	4.8		4.8	4.8
Inrush current (capacitive) (A)														
Contact distance (mm)		<3	<3	<3	<3	<3	<3	<3	<3	<3	<3	>3	>3	>3
Contact material		Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Au	Au	Ag	Ag	Au
EN 60335 cap. 30 conform "G"														
Miscellaneous		momentary function both sides	PCB lined	PCB lined momentary function both sides	installation depth 20.6			momentary function one side	momentary function both sides		momentary function both sides			
Stock version		○	○	○		○	○	○	○		○	○		