

Main

Range	Resi9
Product or component type	Access module
Accessory / separate part category	Enclosure accessory
Range compatibility	Resi9 enclosure

Complementary

Enclosure mounting	Flush
Type of front cover	Cover frame
Door opening side	Reversible
9 mm pitches	26
Number of 18 mm modules per row	1 x 13
Total number of 18 mm modules	13
Provided equipment	1 door
Standards	NF C 15-100
IP degree of protection	IP40
IK degree of protection	IK09 conforming to EN 50102
Net weight	4.4 kg
Quantity per set	1
Width	335 mm
Height	980 mm
Depth	7 mm
Colour tint	White (RAL 9003)
Targeted country	France

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes