

Specifications



Eaton EBMS1253

Eaton Memshield 3 MCB Distribution Board, MEM B, switch disconnecter kit 125A TP incl. isolator

General specifications

PRODUCT NAME	Eaton Memshield 3 MCB Distribution Board other accessory
CATALOG NUMBER	EBMS1253
MODEL CODE	EBMS1253
EAN	5019586158352
PRODUCT LENGTH/DEPTH	120 mm
PRODUCT HEIGHT	150 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	0.539 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	CE

Delivery program

AMPERAGE RATING	125 A
NUMBER OF POLES	Three-pole

Technical data - electrical

VOLTAGE TYPE	AC
VOLTAGE RATING - MIN	240 V
RATED OPERATIONAL VOLTAGE (UE) - MAX	415 V
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	2 kA
LAMP POWER	0 W
RATED SWITCHING CAPACITY	10 kA

Technical data - mechanical

SWITCH TYPE	Other
LAMP TYPE	Other
LAMP SOCKET	Other
WIDTH IN NUMBER OF MODULAR SPACINGS	3
DEGREE OF PROTECTION	IP40
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	3
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	3
BUILT-IN DEPTH	69.5 mm
COLOR CALOTTE	Other

Additional information

IMPRINT/INDICATION	Symbol "arrows"
---------------------------	-----------------

Resources

BROCHURES	eaton-afdd-guidance-brochure-br003010en-en-us.pdf
CATALOGUES	eaton-power-distribution-components-catalogue-ca014013en-en-gb.pdf
INSTALLATION INSTRUCTIONS	IL001180ZU
INSTALLATION VIDEOS	MEM Lighting Power Metering Solutions from Eaton's Electrical Sector

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

