

Main

| | |
|-----------------------------|-------------------------------------|
| Range | Resi9 |
| Product or component type | Flush-mounting rack |
| Nb of 18 mm modules per row | 1 x 18 |
| Nb of horizontal rows | 6 |
| Mounting plate description | Without mounting plate |
| Width | Embedded: 390 mm Total: 408 mm |
| Height | Embedded: 1120 mm Total: 1145 mm |
| Depth | Embedded : 160 mm |
| Colour | White (RAL 9003) |

Complementary

| | |
|--------------------|-------------|
| Enclosure mounting | Flush |
| Enclosure material | Sheet metal |
| Net weight | 6.1 kg |
| Internal depth | 160 mm |

Environment

| | |
|-------------------------|-----------------------------|
| Standards | NF C 15-100 |
| IK degree of protection | IK09 conforming to EN 50102 |

Offer Sustainability

| | |
|----------------------------|--|
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation |  China RoHS Declaration |
| RoHS exemption information |  Yes |