

8563-N-05

Torque wrench DREMOMETER DNR Set 3/4"

155-760 Nm

Code
3107043

ETIM
EC002132

EAN
4002805937822

UNSPSC
27-11-17-15

Country of origin
Germany

eCl@ss
21-04-02-22

Customs tariff number
82041100



Article description

- Torque wrench 155-760 Nm tightening range with test certificate; with extension tube
- Controlled clockwise tightening; 3/4" output drive; plus clockwise rotating 3/4" add-on ratchet
- Classified as per DIN EN ISO 6789-2:2017; adjusted to a maximum permissible +/-3% deviation and thus with a greater precision than the standard-stipulated +/-4%
- Vernier scale - resolution 1.0 Nm
- Made in Germany

Article parts list

DREMOMETER DN 3/4" with vernier 155-760Nm No. 8563-N-00 ,Extension tube DR/DX ALU No. 8571-80 ,Ratchet head No. 754-04

Article information

Contents (Qty of pieces)	1	Torque (max.) [N·m]	760 Nm
Net weight [kg]	3,005 kg	Precision +/-	+/- 3 %
Total length [mm]	812 mm	Direction of tightening	Right
Total width [mm]	45 mm	Fixed setting	no
Total height [mm]	35 mm	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	3/4"	Graduation	10
Drive connector square (male)	20 mm	vernier Nm	1 Nm
Drive type/drive	Single square	Distance housing - square drive	22,5 mm
Torque (min.) [N·m]	155 Nm		