



ENGLISH

RS Pro Fahrenheit/Centigrade Dial Dry Thermometer Suitable For Various Applications

RS Stock No. 324-8407

Brand RS Pro



Product Details

Centre Back and Vertical 100mm Diameter Immersion Thermometers

Bi-metal element thermometers with applications in the heating and ventilation process, and refrigeration industries

Dual scale

Acrylic Window

Temperature range covers both hot & chilled water applications

Manufactured to DIN 16203

1/2 in. BSP Brass Male Thread

Vertical entry types: [324-8384](#), [324-8413](#), [324-8407](#), [324-8429](#)

Thermometers-Socket Insertion Type

Specifications

Not what you're looking for? Select the attributes you require, then click the button below

<input type="checkbox"/>	Thermometer Type	Dial
<input type="checkbox"/>	Suitable Applications	Heating & Ventilation, Refrigeration Industry
<input type="checkbox"/>	Temperature Scale	Both
<input type="checkbox"/>	Filling Type	Dry
<input type="checkbox"/>	Case Material	Steel
<input type="checkbox"/>	Case Diameter	100mm
<input type="checkbox"/>	Maximum Temperature Sensed	+60°C
<input type="checkbox"/>	Minimum Temperature Sensed	-20°C
<input type="checkbox"/>	Temperature Sensitive Range	-20 → +60°C