

Item	260-410
Description:	Terminal strip for 2 drivers with mounting screws for fixing and similar mounting hole Ø 3.2 mm with mounting foot as rail 35 to 10 double strands



Packing unit 20 pieces

Product Group	9 (MINI-TERMINAL)
section [mm ²]	0.08 to 1.5 mm ²
sections [AWG]	28 - 14 AWG
connection type	CAGE CLAMP [®]
measuring voltage IN	400 V
Surge voltage reference	6 kV
degree of pollution	3
EN amperage	4 A
Weight	33.281 g
Cabling Type	wiring side
strip length [mm]	8 mm
to strip length [mm]	9 mm
strip length [inch]	0.33 in