

Datasheet

Stainless Steel Threaded Plug, 1/8 in R Male

RS Stock number 2952723



Description

- Plug BSP Taper Thread
- Shuts off a circuit end
- Assembly with an Allen key
- Body: Stainless steel 316L

Specifications

- Maximum Working Pressure: 150 bar
- Working Temperature: 20 to 180 °C
- Connection 1: 1/8 in R Male
- Connection Gender 1: Male
- Fitting Type: Plug
- Thread Size 1: 1/8 in
- Thread Standard 1: R

Measurements

- C R1/8
- E1 (mm) 6
- E2 Mini (mm) 3.1
- E2 Maxi (mm) 4.9
- F (mm) 5
- ØG (mm) 9.72
- H (mm) 8
- Weight (kg) 0.003

