

EK EKJB 130 G-2FSH



Sample photo

Order symbol: EKJB 130 G-2FSH
Product nbr: 9996187
Description: Enclosure, PC
Remarks: Grey hinged cover

EAN: 6418074052988
EI. number:
Finland: 3435826
Electric No. Sweden: 9996187

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	280	190	130	EKJ 30-G Cover
inch:	11.0	7.5	5.1	EKJ 80-G Cover
				EKJ 30-T Cover
				EKJ 80-T Cover

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

EKJVT	Mounting plate
EKJXT	Mounting plate Pertinax
EKV 12	DIN-35 Mounting rail
EKV 22	DIN-35 Mounting rail
EKJZR	Extension frame

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Rating:
Ingress Protection (EN 60529): IP65
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Accessories:	
EKJB	Base, PC

Certificates:
Gost R

