



Pushing Performance
Since 1945

Han Gigabit insert F, Cat. 7



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 008 3131
Specification	Han Gigabit insert F, Cat. 7
HARTING eCatalogue	https://harting.com/09140083131

Identification

Category	Modules
Type of module	Han [®] Gigabit module
Description of the module	Insert
Features	Suitable for PoE++

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	8
further contacts	+ shielding
Details	Please order crimp contacts separately. Please order adapter module separately.

Technical characteristics

Conductor cross-section	0.09 ... 0.52 mm ²
Wire outer diameter	≤1.7 mm
Rated current	5 A
Rated voltage	50 V
Rated voltage	50 V AC 60 V DC
Rated impulse voltage	0.8 kV
Pollution degree	3
Rated voltage acc. to UL	30 V



Pushing Performance
Since 1945

Technical characteristics

Transmission characteristics	Cat. 7 _A Class F _A up to 1,000 MHz
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Contact resistance, shielding	≤100 mΩ
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material (shielding)	Zinc die-cast, nickel-plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	1e38d35d-d1be-4585-8e03-95faccd739bf
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL



Pushing Performance
Since 1945

Commercial data

Packaging size	1
Net weight	37 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140187535
eCl@ss	27440218 Module for industrial connectors (data)
ETIM	EC000438
UNSPSC 24.0	39121552