

Product Information



3678ITP100P62

EAN 4031582417425

Fixed castor, Fork made of pressed steel, bright zinc plated, blue passivated, wheel axle with nut, plate fitting.

Wheel centre made of Aluminium, Tread: Polyurethane, casted, precision ball bearing

Technical Data	
Wheel diameter	100 mm
Width of Tread	40 mm
Size of Plate	105 x 85 mm
Plate hole centres	80/77 x 60 mm
Plate hole	9 mm
Overall height	130 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	1.06 kg
Hardness of tread	Shore A 92
Load capacity	300 kg
Load capacity (static)	600 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+