

**ZMA40/75** **Precision locknut**

Precision locknuts ZMA, locking pegs, radially arranged, heavy series

Technical information**Main Dimensions & Performance Data**

d	M40X1,5	Thread
D	75 mm	Outside diameter
h	30 mm	Height
M _A	15 Nm	Mounting torque set screw
F _{aB}	520,000 N	Breaking load, axial
M _L	95 Nm	Breakawag
M _{AL}	55 Nm	Mounting torque reference
M _M	6.72 kg*cm ²	Mass moment of inertia
≈m	0.726 kg	Weight

Dimensions

d ₁	69 mm	Plant diameter outside
t	2.5 mm	Hight retaining slot
b	6 mm	Width retaining slot
c	15 mm	Distance bore
m	M8	Threaded - threaded pin