





Technical data

51218

One direction thrust ball bearings

VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	90 mm
D - External diameter	135 mm
T - Thrust bearing height	35 mm
rs - Min fillet radius	1,1 mm
Mass	1,7 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	117000000 mN
C0a - Static axial load rating	325000000 mN
Cua - Limit axial load rating	139000000 mN
N lim - Oil lubrication limit speed	12000 °/s
N lim - Grease lubrication limit speed	8400 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	108 mm
da min - Min shoulder diameter IR	117 mm

