



6304 - EQUAL AND UNEQUAL TEE



maximum working pressure	16 bar 2 MPa 232 psi
working temperature	-10 to 130 °C 14 to 266 °F 263 to 403 °K
vacuum capability	755 mm Hg
body	BIO-BASED POLYMER
'O'-rings	EPDM
gripping ring	STAINLESS STEEL

Part Nb	ØD (MM)	ØD1 (MM)	ØG (mm)	H (mm)	L_2 (mm)	(kg)
	All ▾	All ▾	All ▾	All ▾	All ▾	All ▾
6304 04 00WP2	4	4	8.5	20	15.5	.004
6304 06 00WP2	6	6	10.5	23	18	.006
6304 08 00WP2	8	8	13.5	29	22.5	.006
6304 10 00WP2	10	10	16	34.5	26.5	.009
6304 12 00WP2	12	12	19	40	31	.014
6304 16 00	16	16	27	53	39	.063
6304 16 12	16	12	27	53	39	.037