

FEATURES

- **Stainless steel material or steel options**
- **M4 fixing for catch and latch**
- **25kgf operating tension**
- **Catch to latch distance 44mm**
- **Hand operated and easy to use**
- **Draw latch with over centre fastener**

Zinc Plated Steel Toggle Latch

RS Stock No.: 197-4110



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO basic compact toggle latches which have a length of 50 mm, a width of 22.4 mm and depth of 12mm Toggle latches are a type of mechanical fastener and are also known as over centre fasteners, draw latches, and quick release fasteners and offer secure and easy fastening when locked. The unique cam action design makes the toggle latch strong and reliable and the quick release function means it can open quickly. When choosing a toggle latch you need to consider the maximum load to which it will be subject to as each latch has been designed for a maximum load. RS PRO have a great range of toggle latches and door latches to suit large or small-scale applications including high strength latches, lockable, adjustable and non-adjustable options.

[197-4110](#) - Toggle Latch Steel and Catch Plate

[197-4126](#) - Toggle Latch Stainless Steel and Catch Plate

General Specifications

Material	Steel
Finish	Zinc
Operating Tension	25.0kgf
Application	Cases and containers, Enclosures, Industrial machinery, food containers and marine equipment, light duty applications.

Mechanical Specifications

Dimensions	50mm x 22.4mm x 12mm
Depth	15mm
Length	50mm
Width	22.4mm

Approvals

Compliance/Certifications	2011/65/EU and 2015/863
----------------------------------	-------------------------



Dimensional Drawing:





