

S476 - Berlin Hi-Vis Executive Vest

Collection: Vest-Port

Range: High Visibility

Shell Fabric: 100% Polyester, Warp Knit 125g

Product information

Revolutionary in its design, the executive vest combines the light weight of a waistcoat with the practicality of pockets for those situations when a jacket may be too warm. A clear ID pocket for security passes and cards complements this unique garment.

Standards

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
ANSI/ISEA 107 TYPE R CLASS 2

Vest-Port

The Vest-Port™ extensive range of vests covers the varied demands of the work environment from core styles to the revolutionary "Executive" design, which is now available in both summer and winter weights.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Features

- Front zip opening for easy access
- 7 pockets for ample storage
- Two lower patch pockets
- Phone and pen holder pocket
- Dual ID holder allows use of both portrait and landscape ID card display
- Radio loop for easy clipping of a radio
- D-ring for keys or ID cards
- Available in sizes from XS to 7XL
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)
- CE certified



S476 - Berlin Hi-Vis Executive Vest
Commodity Code: 6110309100

Test House

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)

Sebenhirtenstrasse 12A

1230, Austria

Contact: Marion Pfeiler

Cert No: VN605 152068

ITS Testing Services (UK) Ltd. (Intertek) (Notified Body No.: 0362)

Centre Court

LE19 1WD, UK

Cert No: LECFI00382678

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
S476YERXS	Yellow	43.0	28.0	48.0	0.2280	0.0578	5036108256297	15036108745200
S476YERS	Yellow	43.0	28.0	48.0	0.2300	0.0578	5036108137374	15036108651945
S476YERM	Yellow	43.0	28.0	48.0	0.2000	0.0578	5036108137381	15036108651938
S476YERL	Yellow	43.0	28.0	48.0	0.2200	0.0578	5036108137398	15036108651921
S476YERXL	Yellow	43.0	28.0	48.0	0.2800	0.0578	5036108137404	15036108651952
S476YERXXL	Yellow	43.0	28.0	48.0	0.2540	0.0578	5036108137411	15036108651969
S476YERXXXL	Yellow	43.0	28.0	48.0	0.2720	0.0578	5036108137428	15036108651976
S476YER4XL	Yellow	43.0	28.0	52.0	0.2820	0.0626	5036108166299	15036108706102
S476YER5XL	Yellow	43.0	28.0	52.0	0.2820	0.0626	5036108166305	15036108706119
S476YER6XL	Yellow	43.0	28.0	52.0	0.3600	0.0626	5036108218745	15036108706126
S476YER7XL	Yellow	43.0	28.0	52.0	0.3160	0.0626	5036108218752	15036108706133