

datasheet for MMS 2030
article number: 972341001



product description:	order number: 972 341-001
description:	Test equipment set for safety applications DIN EN 61010-031, as accessories for measuring instruments. contents: 1 x Test tip PRUEF 2700 black (972 319-100), 1 x Test tip PRUEF 2700 red (972 319-101), 1 x Clamp-test tip KLEPS 2600 black (972 306 100), 1 x Clamp-test tip KLEPS 2600 red (972 306 101), 1 x measuring line MLS WG 100/1 black (934 095-100), 1 x measuring line MLS WG 100/1 red (934 095-101)
typ:	MMS 2030
system:	4mm safety system
order number:	972 341-001
clamping range:	30mm
technical data	
measurement category	CAT III // PRUEF 2700: CAT II
norm	DIN EN 61010-031
pin dimensions	4mm
type of contact:	pin (spring-loaded)
type of termination:	4mm diameter pin
cable type:	LEH-XY
cable specification:	highly flexible lead
wire stranding:	259 x 0,07
rated voltage:	AC/DC 1000 V
cable length:	100cm
conductor size:	1mm ²
cable material:	PVC
cable color:	each article in black and red
environmental conditions:	
temperature range:	-15 °C to +70 °C