

Product information

260MM MITRE SAW



Satisfying the professional's needs

LS1018L

Blade Diameter	260 mm
Max mitre range	60 - 47 °
Max mitre cut at 90°	91 x 310 mm
Max mitre cut at 45°	91 x 220 mm
Bore Diameter	30 mm
Max bevel range	45 - 45 °
Noise sound pressure	97 dB(A)
Noise sound power	103 dB(A)
Noise K factor	3 dB(A)
Input wattage	1430 w
No Load Speed	4300 rpm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Chipboard	2.5 m/sec ²



- Soft start
- Electric brake
- Double Insulation
- Bevel cutting 45 degrees left and right.
- Built in laser guide.

Details correct as of: 29-7-2015

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makita.com