

## tesa® 53311

### High-Performance Strength Fiberglass Reinforced Filament Tape

tesa® 53311 is a very high strength polyester backed fiberglass reinforced filament tape.

tesa® 53311 has an aggressive and high shear resistant adhesive system.

### Main Application

- Pallet securing
- Bundling of very heavy goods
- Closure and reinforcement of very heavy cartons
- Securing of coils

### Technical Data

▪ Backing material	glassfiber & PET	▪ Adhesion to steel	5 N/cm
▪ Total thickness	190 µm		45.7 oz/in
	7.5 mils	▪ Elongation at break	5 %
▪ Type of adhesive	natural rubber	▪ Tensile strength	583 N/cm
			332.9 lbs/in

For latest information on this product please visit <http://l.tesa.com/?ip=53311>

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.