

# SSPL20/M20/M



M20 SS M TYPE FOR SPL20



Product image  
not available

## General Information

Extended Product Type	SSPL20/M20/M
Product ID	7TBA296030R0379
EAN	5020963053474
Catalog Description	M20 SS M TYPE FOR SPL20
Long Description	Stainless Steel Straight Swivel Fitting with External Thread, Conduit Size 20 Millimeters, Thread Size M20

## Ordering

EAN	5020963053474
Customs Tariff Number	8307103000

## Dimensions

Product Net Weight	.29 lb 131.519 g
--------------------	---------------------

## Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

## Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M20 Thread
Color	Metallic
Material	Stainless Steel
Number of Batteries	0
Product Name	METAL FLEX CONDUIT
Product Type	Liquid Tight Non-Metallic Fitting
Size	NC 20mm

---

UPC	786210259413
-----	--------------

---

---

### Certificates and Declarations (Document Number)

---

Data Sheet, Technical Information	SSPL20/M20/M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SSPL20/M20/M

---

---

### Classifications

---

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

---

---

### Categories

---

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available