



### Auxiliary contacts

Description	Type	Order number	Units/type [pcs]	Weight [kg]
-------------	------	--------------	------------------	-------------

#### Auxiliary contacts for OS Mini

Mounting to the switch mechanism, auxiliary/test contacts. Max. two change over contacts.

##### Change over contacts

	Handle position	Main contacts	Aux. / Test contacts N.O.	Type	Order number	Units/type	Weight
	Test	open open closed	closed open closed				
	0			OA4B1C	1SCA022193R0150	1	0.03

##### Single pole contacts > 3 mm contact gap.

1 NO		OA4B10	1SCA022276R9050	1	0.03
1 NC		OA4B01	1SCA022276R9210	1	0.03

##### Mounting on the side of the switch with aux.contact frame OESAZX 169.

1 NO		MCB-10	1SCA022150R5110	1	0.03
1 NC		MCB-01	1SCA022150R5370	1	0.03

##### Snap-on mounting on the switch, by using a frame OSZ4. IP20.

NO contacts are provided with a positive opening feature. Units/type = 1 piece. Types \_AU have gold plated contacts for harsh environments and low operating voltages.

Description	Type	Order number	Delivery batch [pcs]	Weight /unit [kg]	
1 NO		OA1G10	1SCA022353R4970	10	0.03
1 NC		OA3G01	1SCA022456R7410	10	0.03
1 NO		OA1G10AU	1SCA022436R7910	10	0.03
1 NC		OA3G01AU	1SCA022819R5260	10	0.03

### Mounting frames for auxiliary contacts of OS Mini

	Type	Order number	Units/type [pcs]	Weight [kg]
--	------	--------------	------------------	-------------

Frame for auxiliary contacts OA1G10 and OA3G01 and for fuse monitor. Max. 6 auxiliary contacts can be fitted.

Mounting on the left side of the switch	OSZ4	1SCA022530R0200	1	0.06
---	------	-----------------	---	------

Frame for MCB-\_ auxiliary contacts. Not suitable for side operated switches. Max. 6 auxiliary contacts can be fitted.

Mounting on the right side of the switch	OESAZX169	1SCA022196R9360	1	0.06
--	-----------	-----------------	---	------