

Datasheet

RS Pro Right Angle Cable Mount SMA Connector, Plug, Crimp Termination RG174

RS Stock No: **546-3248**



Product Details

RS Pro right angle cable mount SMA connector plug features a gold plated brass body, gold plated centre contact, silicone gasket and is suitable for use with a variety of RF coaxial cable types. This male connector plug is suitable for applications including Wi-Fi equipment.

Features and Benefits

- Gold plated brass body, gold plated centre contact, silicone gasket
- Suitable for use with a variety of RF coaxial cable types
- Crimp termination method
- Suitable for applications including Wi-Fi equipment

**Specifications:**

Body Orientation	Right Angle
Body Plating	Gold
Cable Type	RG174
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	6 GHz
Polarity	Normal
Size	Subminiature
Termination Method	Crimp
Voltage Rating	500 V
Body Material	Brass
Operating Temperature	-65 to +165°C
Type	SMA
VSWR (Voltage Standing Wave Ratio)	1.21 at 3 GHz