

**Datasheet**

# RS PRO Non Ceramic, High Temperature Universal Millboard

Stock No: 2035133

**Technical Specifications:**

Classification Temperature	1,000°C
Density	1,000 kg/m <sup>3</sup>
Coefficient of Thermal Conductivity	0.1 W/mK
Tensile Strength	3.4 MPa @ 20°C
Flexural Strength	8.0 MPa @ 20°C

## Features & Benefits:

- **Low Shrinkage**
- **Cost Effective**
- **Free of Harmful Fibres**
- **High Temperature Capability**
- **Easy to Cut and Machine**

## Further Technical Specifications

Compression	35 % @ 21 MPa
Moisture Content	1.05%
Loss on Ignition	12%
Linear Shrinkage in 24 hours	0.75% @ 1,000°C
Colour	Beige to Grey