



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #CAT-T4827-CH8172  
Timer Connector Housing



TE Part #CAT-M5833-M2934A  
Male-on-Wire Connector, Micro-MaTch



TE Part #T4110012041-000  
M12 F, 4P GOLD A\_CODE S  
SHIELDED PG9




TE Part #3-2176331-5  
CRGP 2512 6K8 1%



TE Part #2-1445096-4  
MICRO MNL HDR ASSY SINGLE ROW



TE Part #DT15-12PC-B016  
HDR, 12P, GRN, ST, ENH KEY, NI/CU,  
C



TE Part #929975-1  
BU-KONTAKT 2,5MMD



TE Part #1-180908-0  
FF 250 TAB HSG 2P NYLON NAT

Documents

Product Drawings

312 FASTON,PCB TAB,TCBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1217956-1\_E.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1217956-1\_E.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1217956-1\_E.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English

