



Main

Range of product	Canalis
Product name	KS
Product or component type	Empty tap-off unit
Product compatibility	KS
[Ie] rated operational current	50 A at 35 °C
Tap-off unit polarity	3L+N+PE

Complementary

Device application	Low power distribution
[Ue] rated operational voltage	230...690 V depending on protective device
[Uimp] rated impulse withstand voltage	8 kV
[Ui] rated insulation voltage	690 V depending on protective device
Network frequency	50/60 Hz
Tap-off unit disconnection mode	By drawing out
Tap-off unit connector type	With fixed polarity
Door opening size	432.5 mm
Door opening side	Right
Standards	IEC 60439-2 IEC 61439-6
Body material	Plastic
Colour	White (RAL 9001)
Width	356 mm
Depth	103 mm
Height	202 mm
Net weight	2.2 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Earthing system	TT - busbar trunking TN-S - busbar trunking TN-C - busbar trunking IT - busbar trunking TT - tap-off unit TN-S - tap-off unit IT - tap-off unit
-----------------	---

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------

