

## FEATURES

- Wire strippers with knife blades to ensure clean
- Accurate stripping
- Specially contoured comfort grips reduce operator fatigue
- Special Lock Lid Design for easy storage

## RS PRO 155 mm Wire Stripper, 0.4mm → 1.3mm

RS Stock No.: 540-1515



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

From RS PRO, these manual wire strippers are perfect for stripping insulation from a variety of wire sizes. The stripper has knife style blades with six integrated cutting sizes, allowing you sharp and precise control when stripping wire. Combined with the soft grip ergonomic handles and return spring, these RS PRO wire strippers make cable management easier and more efficient.

- [540-1492](#) is a manual wire stripper for wire sizes of 10 to 20 AWG
- [540-1509](#) is a manual wire stripper for wire sizes of 20 to 30 AWG
- [540-1515](#) is a manual wire stripper for wire sizes of 16 to 26 AWG

## General Specifications

<b>Cable Type</b>	Stranded
<b>Stripping Range</b>	0.13mm to 2.07mm
<b>Minimum Size</b>	0.4mm
<b>Maximum Size</b>	1.3mm
<b>Material</b>	High carbon steel sheet (sk-5) for body of crimping tools, low carbon steel (s1018c) for lock screws & rivet, medium carbon steel (ss41) for lock lid, PVC grip and spring steel for high tension return spring
<b>Finish</b>	Grounding cut edges, chemical black finish and red colour vinyl grip
<b>Applications</b>	Wire strippers are primarily used by electricians or mechanics but are equally at home in any DIY toolbox.

## Mechanical Specifications

<b>Overall Length</b>	155mm
<b>Hardness</b>	Heat treated to HRC: 49~ 50.5 (whole body) and HRC: 30 ~ 40 (screws)

## Approvals

<b>Compliance/Certification</b>	ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007
<b>VDE Approved</b>	No

