



Leiterquerschnitt / wire gauge: 2,5mm<sup>2</sup> / AWG 14  
 Abisolierlänge / stripping length: 9mm

All Dimensions in mm Original Size DIN A 4			Techn. Character.			Nicht tolerierte Maß / Free size tolerances		
				Dat.	Name	Maßstab / Scale  2:1	Han C Stiftkontakt gedreht 40A/ Han C male contact turned 40A versilbert / silver plated	
			Detail.	14.01.09	Ho			
			Insp.		Tie			
			Stand.					
B	09.11.10	ML	HARTING Electric GmbH & Co. KG				TB 09 32 000 6105	
A			D-32339 Espelkamp					
Mod.	Dat.	Name					Sub. TB 09 32 000 6105 v. 20.12.05	
							Blatt / page	