



ENGLISH

Datasheet

Stock No: 499-2717

## RS Pro, 3/8 in BSP Stainless Steel Y Strainer



### Product Details

#### Class 800 Stainless Steel Y-Strainer

RS Brand stainless steel screwed end Y-strainers for use when the amount of solids to be removed is small. They can be installed in both horizontal and vertical positions. Available in a variety of sizes.

#### Features:

1/4" - 3" (DN8 - DN80)

W.P: 800WOG (PN50)

W.T: -20°C - 200°C (-4°F - 392°F)

Investment casting

Thread type: ASME B1.20.1 (NPT) DIN2999 & BS21 ISO 7/1 & EN10226

#### Material:

Body, Cap & Drain Plug - ASTM A351-CF8M

Screen - AISI 316

Seal & Gasket - PTFE

#### Y Type Strainers

For the efficient removal of contaminant particles in liquid pipelines.

## Specifications:

Strainer or Filter	Strainer
Suitable Media	Liquid
Connection	3/8 in BSP
Body Material	Stainless Steel
Connection Size	3/8in
Thread Standard or Connection Type	BSP