

Reinforced nitrile gloves, combining comfort with superb mechanical and chemical protection

- **Heightened durability and protection:** Versatile by design, AlphaTec® 39-124 nitrile-coated gloves combine durability, mechanical protection and chemical resistance, while ensuring superb dexterity and wet and dry grip
- **Advanced ergonomics:** These flexible work gloves are longer than the AlphaTec® 39-122 model, featuring a natural shape with curved, pre-flexed fingers and winged thumbs, for lesser hand fatigue and greater comfort
- **Food handling compliance:** AlphaTec® 39-124 food safety gloves comply with FDA food handling requirements, making them suitable for various food processing and service applications

Industries

- Automotive Aftermarket
- Metal fabrication

Applications

- Oil, fluids and filter change
- Handling materials with sharp or rough edges
- Applying finish to materials, products
- Adjusting panels parts components
- Production line support & maintenance
- Equipment repair & maintenance
- Assembly and disassembly of equipment



Previously known as: Sol-Knit™ 39-124

Key Features

- **Nitrile coating:** For highly durable abrasion-resistant gloves
- **Ergonomic design:** High-dexterity work gloves ideal for light-duty tasks
- **FDA approval:** Compliant with relevant food handling requirements

Vulcanization Chemical Accelerators

- Zinc 2-mercaptobenzothiazole

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards

ANSI/ISEA 105-2024



0493

EN388: 2016



4111B

EN 407



XTXXX

EN ISO 374-1:2016
Type B



JKT

EN ISO 374-5:2016



Specifications

BRAND STYLE	DESCRIPTION	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 39-124	Liner Material: Interlock cotton Coating Material: Nitrile	7, 8, 9, 10	350 / 13.8	Green	• 12 pairs in a bag; 6 bags in a carton

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada Inc.
105, rue Lauder
Cowansville (Québec)
J2K 2K8, Canada
T: 1 800 363-8340
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:
www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.