

Datasheet

ENGLISH

ECP-11 UK series

11W plug-in power supply




Features

- No load power consumption
- Protections: short circuit//overload voltage/overload current
- UK and European versions available
- Compact and light-weight
- Withstands operating environment of 0-40°C
- Efficiencies up to 86%
- 3 year warranty
- External switch mode plug-top power supplies
- Efficiency level V, Conforms to Energy-related Product Directive 2009/125/EC
- Energy saving power supply
- Class II double insulated
- 1.2 metre (approx.) output lead with
 2.1x5.5x9.5mm centre positive output connector
- Regulated output
- EMC compliance to EN 55022 Class B

Part number	Voltage	Rated current	Voltage range	Rated power	MTBF
7262747	5V	2.2A	4.7 ~ 5.3V	11W	100,000hrs min. MIL-HDBK – 217F (25° ^C)
7262741	7.5V	1.47A	7.1 ~ 7.9V		
7262750	9V	1.22A	8.5 ~ 9.5V		
7262753	12V	0.92A	11.4 ~ 12.6V		
7262757	15V	0.73A	14.25 ~ 15.75V		
7262766	18V	0.61A	17.1 ~ 18.9V		
7262769	24V	0.46A	22.8 ~ 25.2V		

Mechanical specification



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.