



Part Number : [16021112](#)
Product Description : SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Reel
Series Number : 71851
Status : Active
Product Category : Crimp Terminals
Engineering Number : 71851-0004
Packaging Alternative : [16021116](#) (Bag)



Documents & Resources

Drawings


[016021112 sd.pdf](#)
[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)

Specifications

[PS-70400-001.pdf](#)
[PS-71851-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	71851
Description	SL Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 30-24 AWG, Reel
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Name	SL
UPC	800753595781

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.060/g
Packaging Type	Reel
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52mm max.
Wire Size (AWG)	24, 26, 28, 30

Wire Size mm ²	N/A
---------------------------	-----

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Insertion Tool for 70021,70028, 70110, 71851 Terminals / Extraction Tool for 91821 Terminals	<u>11020022</u>
Extraction Tool for SL Terminals, 36-22 AWG	<u>11030036</u>
Hand Crimp Tool for SL Crimp Terminals, 30-24 AWG	<u>2002187000</u>
FineAdjust Applicator for SL Female Crimp Terminal, Insulation OD 0.63-1.00mm, 30-24 AWG Wire	<u>639001500</u>
FineAdjust Applicator for SL Female Crimp Terminal, Insulation OD 1.01-1.52mm, 30-24 AWG Wire	<u>639003100</u>
T2 Terminator Tooling Die	<u>639103100</u>