



Product Compliance


For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247)<br>Does not contain REACH SVHC |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free                                           |
| Solder Process Capability                     | Not reviewed for solder process capability                                                                                    |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 184154-1  
2 POS. END CAP HSG., KEY D



TE Part # 184160-1  
2 POS. END CAP HSG., KEY K




TE Part # 184162-1  
2 POS. END CAP HSG., KEY M



TE Part # 184375-1  
2 POS PLUG ASSY W/ SIDECAP PRO



TE Part # 184169-1  
2 POS. CAP HSG., KEY G




TE Part # 184152-1  
2 POS. END CAP HSG., KEY B



TE Part # 184373-2  
CONTACT, RECEPTACLE, .070 TYPE



TE Part # 184170-1  
2 POS. CAP HSG., KEY H



TE Part # 184060-1  
6 POS./6 CIRC PLUG ASSY, KEY A



TE Part # 184139-1  
WIRE SEAL,RUBBER,SENSOR,BLUE



TE Part # 184002-1  
2 POS. PLUG ASSY, KEY B, GRAY



TE Part # 184166-1  
2 POS. CAP HSG., KEY D



TE Part # 184095-1  
RECPT, CONTACT .070, AUPHBZ




TE Part # 184030-1  
RECPT, CONTACT 070, AUPHBZ




TE Part # 184141-1  
WIRE SEAL,RUBBER,SENSOR,PURPLE, LIM




TE Part # 184140-1  
WIRE SEAL,RUBBER,SENSOR, ORANGE



TE Part # 184161-1  
2 POS., END CAP HSG., KEY L



TE Part # 184157-1  
2 POS. END CAP HSG., KEY G



TE Part # 184158-1  
2 POS. END CAP HSG., KEY H



TE Part # 184212-2  
2 POS. PLUG ASSY, KEY A NATURAL


Customers Also Bought



TE Part #1670364-1  
COVER,180 GROUP C



TE Part #282956-1  
SPLASH PROOF FEM CONN ASSY



TE Part #638245-1  
RECEPTACLE ASSY,4P SEALED,JPT



TE Part #2050052-1  
4POS 2.8MM SENSOR PLUG ASSY.



TE Part #66104-7  
III+ SKT, 24-20, TIN-LEAD, STRIP



TE Part #1-1703773-1  
6POS, TAB 1.6X0.6, PIN HSG, ASSY,




TE Part #184311-1  
ASSY, PLUG HSG 3 POS, KEY A



TE Part #1924779-1  
WIRE DRESS ASSY, 96P GPEC II



TE Part #1986711-2  
SCREWLESS, SW, 2P, 5.0 PCB



TE Part #881590-1  
ECONOSEAL TAB .070

Documents

Product Drawings

2 POS. PLUG ASSY, KEY D, GREEN

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_184006-1\_C.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_184006-1\_C.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_184006-1\_C.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Positioning the Double Lock Plate

English



184006-1  
2 POS. PLUG ASSY, KEY D, GREEN

