

FEATURES

- **LED Technology:** Provides energy-efficient lighting with reduced power consumption compared to traditional lighting.
- **6000 K Colour Temperature:** Offers a bright, cool white light suitable for detailed tasks and enhancing visibility.
- **Lifespan of 50,000 Hours:** Ensures long-term use with minimal maintenance requirements.
- **Luminous Flux of 2600 to 4800 lm:** Delivers high brightness to illuminate large areas effectively.
- **IP20 Rating:** Suitable for indoor use, protecting against solid objects over 12 mm.
- **Voltage Range of 220 to 240 V:** Compatible with standard electrical systems.

RS PRO LED Batten Light, 6000 K Colour Temperature

RS Stock No: 286-468



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

Product Description

The RS PRO LED Batten Light is designed to deliver efficient and reliable lighting solutions for a variety of environments. With a colour temperature of 6000 K, it provides a bright, cool white light ideal for workspaces and commercial settings. This batten light offers a long lifespan and energy-efficient performance, making it a cost-effective choice for continuous use.

General Specifications

Anti-corrosive	No
Batten Type	LED
Colour	Cool White, Daylight White, Warm White
Colour Temperature	6000 K
Dimmable	No
EU Energy Efficiency Rating	D
Lamp Type	LED
Lifespan	50000 h
Luminous Flux	2600-4800 lm
Number of Lamps	1
Product Type	Batten Light
UK Energy Efficiency Rating	D

Mechanical Specifications

Depth	73 mm
Length	1170 mm
Width	60 mm

Protection Category

IP Rating	IP20
-----------	------

Electrical Specifications

Power	21-36 W
Voltage	220-240 V

Approvals

Standards/Approvals

BS EN 60598-1

