



ENGLISH

Datasheet

Stock No: 123-7929

RS Pro Candle 5.4W (40W) 2700K 470lm Non Dimmable Frosted Lamp



Specifications:

Lamp Base: B22

Lamp Shape: CANDLE

Wattage: 5.4W

Voltage Rating: 220-240V

Length: 98mm

Diameter: 35mm

Current Rating: 54mA

Frequency Range: 50Hz

Electric Current: AC

Features:

The Base Colour is Matt white Candle Frosted finish. Material is Plastic with polycarbonate and Nickel plated brass with the lamp fixing pendant, chandelier or wall.

Heat Graph: Warm

2700 K

