

Datasheet

MER - 2/PF

RS Stock number 811-8235



Specifications:

No. of Poles:	2 Pole + Earth
Reference Standards:	DIN-43650, ISO 4400
Terminals:	Solder-type
Mounting:	Screw-type
Permissible Temp. With/Without Load:	0 deg.C to 90 deg.C
Approvals:	VDE (On-request)
V/A Rating:	10 A, 250 VAC
Material For Rubber Gasket:	Nitril / Silicon
Material Body:	Polyamide
Insulation Resistance at 500VDC:	100 M Ohms min.
H. V. Breakdown Test:	2 KV AC for 1 Minute
Current Carrying Parts Contact:	Copper Alloy, Tin Plated
Contact Resistance:	20 m Ohms max. (Initial)
Colours:	Black
Type:	Flat Plug

Unit mm

