HellermannTyton

Technical data sheet

Article number:
924-00419 QDM2-6

Product Group	Quick Disconnect Male Funnel Entry
Product Family	Double Grip Pre-Insulated Terminals
Material	Brass (BS), Polyvinylchloride (PVC)
Colour	Blue (BU)

Application Range	Low Voltage
Conductor Size Range mm²	1.5-2.5 mm²
Diameter (D)	4.9 mm
Length (L)	22.5 mm
Length (L2)	11 mm
Length (L3)	11.5 mm
Max Current	15 A
Max Voltage	300 V
Operating Temperature	+75 °C
Package Content	100 pcs.
Package Content packed in	bag
REACh Reg. Art.33 does not contain SVHC	Yes
ROHS compliant	Yes
Width (W)	6.3 mm

RoHS

created on 11. May 2026, 12:23 pm

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.