

Multi tool LXT®

DTM52

18V • 10 000 - 20 000 min⁻¹

Multi-tool for cutting, polishing, grout removal and other applications.

A handy 18V LXT® multi-function tool for a variety of cutting and polishing applications in construction and renovation projects, compatible with STARLOCK MAX. Equipped with a tool-less accessory clamp and the oscillating rate can be adjusted between 10 000 and 20 000 min⁻¹.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Orbits per Minute	10000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,8 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{pA})	72 - 79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Sanding	≤ 2,5 m/s ²
Tool weight with battery	1,7 - 2,0 kg
Product Dimensions (L x W x H):	332 x 95 x 125 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Vibration Uncertainty (K Factor), Sanding	1,5 m/s ²
Vibration Level, Cutting With Plunge Cut Saw Blade	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting With Plunge Cut Saw Blade	1,5 m/s ²

User benefits

- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Soft start for smooth start-ups
- Anti-restart function minimises accidental start-up
- The rubber coating on the handle ensures a firm working grip
- Battery protection system automatically shuts off power when the battery level is low
- 12 Angle settings at every 30° from 0° to 360°

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing