

## Label sheet, DIN A4 - BMKL 25X 8 WH CUS - 0824249

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Label sheet, DIN A4, can be ordered: Sheet, white, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 25 x 8 mm



The figure shows a version of the article

### Why buy this product

- ✓ The unperforated SK U ... sheets are available for custom label designs
- ✓ These labels have been specially developed for laser printers
- ✓ Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- ✓ Can be printed on all commercially available laser printers



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 046356 351249 |
| Weight per Piece (excluding packing) | 9.0 g                                                                                                   |
| Custom tariff number                 | 39199000                                                                                                |
| Country of origin                    | Germany                                                                                                 |
| Note                                 | Made to Order (non-returnable)                                                                          |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 25 mm |
| Width (a)  | 8 mm  |

#### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Ambient temperature (operation) | -20 °C ... 80 °C |
|---------------------------------|------------------|

#### General

|                       |               |
|-----------------------|---------------|
| Color                 | white         |
| Base element material | Polyester     |
| Components            | Silicone-free |

## Label sheet, DIN A4 - BMKL 25X 8 WH CUS - 0824249

### Technical data

#### General

|                                     |                             |
|-------------------------------------|-----------------------------|
| Material                            | Polyester                   |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels         | 224                         |
| Number of individual labels per row | 7                           |
| Marking mounting type               | Adhesive                    |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |