

Datasheet

## RS Pro Electrolytic, Magnetic 22 mm Push-Fit Scale Inhibitor, 1.08L/s

RS Stock No: **738-2738**



### Product Details

RS Pro electrolytic & magnetic push-fit scale inhibitor maintains the flow rate up to 1.08 L/s. This dual purpose unit can be fitted on the cold water mains through push-fit connection of 22 mm, to prolong the life of heating appliances such as a boiler, shower, or cylinder. It induces a single polarity into the water, prolonging the build up of lime scale as per the current building regulations.

### Features and Benefits

- CalCombi mini combination magnetic and electrolytic scale inhibitor
- Push-fit fittings, 22 mm unit fixed, 22 to 15 mm stem adapters x 2 (including inserts)

**Specifications:**

Connection	22 mm Push-Fit
Scale Prevention Mechanism	Electrolytic, Magnetic
Thread Standard or Connection Type	Push Fit
Connection Size	22 mm
Maximum Flow Rate	1.08 L/s
Diameter	32 mm
Finish	Nickel Plated
Length	105 mm
Material	Copper