

MLFB-Ordering data

6SL3203-0BE15-0VA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	Connections
-------------------	--------------------

Input

Number of phases	3 AC
Line voltage	200 ... 480 V

Output

Rated current	5.0 A
---------------	-------

Mechanical data

Dimensions

Width	55.0 mm
Height	170.0 mm
Depth	130.0 mm
Degree of protection	IP20 / UL open type
Net weight	1.5 kg

Line side

Version	screw-type terminal
Conductor cross-section	0,3 ... 10,0 mm ²

Load side

Version	Screw-type terminals
Cable length	20.00 m

PE connection

Version	On housing with M6 screw studs
---------	--------------------------------