

Previously known as: PowerFlex® 80-600



Cut



Heat



Heavy Duty

Durable, cut-resistant work gloves, blending comfort with firm grip performance

- **Enhanced grip:** ActivArm® 80-600 industrial gloves' natural rubber latex coating features a raised crinkle finish, enhancing grip performance in both dry and wet conditions
- **Advanced defenses:** These abrasion-resistant gloves feature a natural rubber latex coating and a Kevlar® knitted liner, meeting ANSI/ISEA 105-2024 CUT A2 and EN ISO C standards, allowing workers to safely handle glass, metal, and plastics.
- **Added convenience:** ActivArm® 80-600 thermal work gloves also come in varying sizes, to cater for all workers and prevent workplace injuries



Industries

- Metal fabrication

Applications

- Forging operations
- Extruding, bending and punching shapes

Previously known as: PowerFlex® 80-600

Key Features

- **Raised crinkle finish:** Excellent wet and dry grip performance
- **Kevlar® knitted liner and rubber coating:** Moderate cut resistance
- **Varied sizing options:** For quality hand protection that caters to all

Vulcanization Chemical Accelerators

- Dithiocarbamate
- Natural rubber proteins
- Zinc 2-mercaptobenzothiazole

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



X444C

EN 407



X2XXXX



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® 80-600	Finishing: Palm Coated Coating Material: Natural Rubber Latex Liner Material: Kevlar® Cuff Style: Knitwrist	10	7, 8, 9, 10	250-280 mm/ 9.64-11.02in	Blue	12 pairs/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell®, and™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.