

183100240300

PIR movement and presence detector 10 A



This image is for illustrative purposes only and therefore may not represent the exact product code. Colours may vary.

TECHNICAL DESCRIPTION:

Rilevatore di movimento, Installazione da interni - montaggio ad incasso o a controsoffitto, 1 interruttore unipolare, 10 A, Programmazione: standard, Circuito contatti: contatto libero da potenziale (contatto pulito), Tipo di alimentazione AC/DC, tensione di alimentazione nominale 24 V, funzionamento da 19.2 a 26.4 V (AC)/(DC), potenza nominale 2 VA (AC) / 1 W (DC), temperatura ambiente da -10 a +50 °C

BROWSE PRODUCT PAGE

Technical Features:

|                                                           |                                                                                                                                                                                                                                                              |
|-----------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Commercial Description:                                   | PIR movement detectors for indoor installation – false ceiling mount. 1 NO 10 A.                                                                                                                                                                             |
| Contact configuration:                                    | 1 NO                                                                                                                                                                                                                                                         |
| Dimensions:                                               | 80x4.2x80 mm                                                                                                                                                                                                                                                 |
| Manageable with app:                                      | NO                                                                                                                                                                                                                                                           |
| Protection category:                                      | IP 40                                                                                                                                                                                                                                                        |
| Rated contact voltage:                                    | 250 V AC                                                                                                                                                                                                                                                     |
| Rated current (contacts):                                 | 10 A                                                                                                                                                                                                                                                         |
| Supply:                                                   | AC/DC supply version                                                                                                                                                                                                                                         |
| Type of installation:                                     | Indoor ceiling installations – recessed mounting                                                                                                                                                                                                             |
| Certifications and quality approvals (according to type): |    |

The information, technical details, data and features contained in this document are subject to change or modification at any time.  
It is for information purposes only and does not form the basis of a contract.

Need more information?  
[Contact our sales](#) [Find a dealer](#)