



Product data sheet

Power tools for trade & industry

Cordless Planer

PRO GHO 12V-20



First professional 12 V planer for a new level of tool control

The most important data

Planing width, max.	56 mm
Planing depth	0 – 2 mm
Rebating depth	0 – 17 mm

Part Number 0 601 5A7 070

Technical data

Technical data

No-load speed	14,500 rpm
Planing depth	0 – 2 mm
Rebating depth	0 – 17 mm
Planing width, max.	56 mm
Weight excl. battery	1.5 kg
Packaging dimensions (width x length x height)	159 x 253 x 122 mm

Noise/vibration information

Total vibration values

Vibration emission value ah	1.5 m/s ²
Uncertainty K	2.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cordless freedom of movement delivers best operability in every working position
- EC-brushless motor and 12 V system make for compact tool design
- Optimized balance point for comfortable and ergonomic handling



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

