

Impact Wrench XGT®

TW001G

40V max • 3/4" • 1 800 Nm • 0 – 1 800 min⁻¹

High torque, brushless impact wrench with electronic four stage power settings for heavy-duty work

A powerful, brushless 3/4" drive impact wrench with a fastening torque of up to 1 800 Nm. Electronic 4 stage power selection. Equipped with 2 x twin LED light for added lighting, this tool is ideal for applications that require high fastening torque.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Brushless Motor	✓
No load speed	0 - 950 / 1150 / 1400 / 1800 min ⁻¹
Max Fastening Torque Impact Drill	450 / 840 / 1500 / 1800 Nm
Nut-busting torque	2050 Nm
Tightening Capacity Standard Bolt	M12 - M36
Impacts per Minute (IPM)	0 - 1900 / 2200 / 2400 / 2500 min ⁻¹
Drive Square	3/4 "
Sound Power Level (L _{WA})	111 dB(A)
Sound Pressure Level (L _{pA})	103 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	3,9 - 5,1 kg

User benefits

- Brushless maintenance-free and long-life motor
- 3 modes of reaction time for automatic stop available both in forward and reverse rotation modes
- Electronic 4 stage impact power selection for added versatility
- Reverse rotation Auto Stop mode stops after the bolt/nut loosened enough
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

■ Optional AC

191G67-2

Extension handle



■ Other

User manual

Parts drawing