

Literature holder FLEXIPLUS A4 landscape magnetic

Article number	1709021060	Sales unit quantity	1 Piece
Colour	Black	Sales unit EAN	4005546742618
Packaging unit	piece	Packing weight (gross)	402 G
Base EAN	4005546742618	Country of origin	DE



Product description

- Literature holder with magnetic fixing for information materials in A4 landscape format
- Ideal for information materials on metallic walls in showrooms, in waiting areas and at trade fairs and in production areas.
- Load capacity of approx. 2 kg
- Inner dimension compartment: 340 x 250 x 23 mm [W x H x D]

Product features

Outer width (mm)	340
Outer height (mm)	200
Outer depth / length	105 mm
Format / Format for	A4+
Orientation Format	Landscape
Brand	DURABLE
Exeternal wall mounting width (mm)	105

Literature holder FLEXIPLUS A4 landscape magnetic

Exeternal wall mounting height (mm)	200
Exeternal wall mounting depth (mm)	340
Inner width (mm)	320
Inner height (mm)	180
Inner depth (mm)	23
Number of Sections	1
Opening for documents	Top
Extendable	No
Recessed slot for easy access	No
Max. load capacity	Up to approx. 2 kg
Country of Origin	Germany
Base / mount type	Magnetic wall mount