

HL40

WIDE ANGLE FLOOD BEAM

300 LUMENS | 30M BEAM | 14H

Whether you want to put it on your hard hat or directly on your head, the HL40 provides a full field of view. The Wide Angle Flood Beam is optimal for illuminating large areas with its ultra-wide circular beam. The headlamp is extremely versatile as you can cycle through the high output or low output with the ease of a switch on the bezel.

With Coast's commitment to quality, the HL40 Headlamp is impact resistant, weather resistant and its LED is virtually unbreakable. The HL40 Headlamp is backed by Coast's lifetime warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.

BATTERY LOCATION	Back	LIGHT OUTPUT (HIGH)	300 Lumens
BATTERY TYPE	3 x AAA (Alkaline)	LIGHT OUTPUT (LOW)	100 Lumens
BEAM DISTANCE (HIGH)	98 ft / 30 m	RUNTIME (HIGH)	3 h 30 min
BEAM DISTANCE (LOW)	55 ft / 17 m	RUNTIME (LOW)	14 h
INCLUDED	3 x AAA Batteries Hardhat Clips	WEIGHT	4.4 oz / 125 g



HARDHAT COMPATIBLE

Rugged enough for the outside of the hardhat. COAST headlamps with Hardhat Compatible design include clips for attaching the light to the hat.



HIGH/LOW

Control your light power with the push of a button. Cycle between High power and low power options.



HINGED BEAM

Up, down, or straight ahead. All COAST headlamps feature a hinged, tilting head so that you can adjust the light's direction and see right where you're looking.



WATER RESISTANCE

Don't worry about the weather. COAST lights that have passed the IPX4-level water resistance test are splash-resistant and built with durable materials that stand up to nature.



WIDE ANGLE FLOOD BEAM OPTIC

See the whole scene at once. The Wide Angle Flood Beam illuminates the broadest possible area with vivid, consistent light from edge to edge. At 6 feet / 1.8 meters distance, the beam shines a clear circle up to 11.5 feet / 3.5 meters in diameter.